



Safety System Products

# Check list high speed roll doors

Date .....

End customer .....

Customer .....

Project/Kommission .....

### Contact person

name .....

phone .....

mail .....

### Type

NORDIC 344protec

NORDIC 344rollback

.....

## Speed roll doors

### Motor side

left

right

### Motor orientation

upwards

to the outside

downwards

to the inside

### Special environmental conditions

.....

### Clear width

.....

### Clear height

.....

### Mounting type

freestanding

embedded in protective fence

### Available space around the opening

over .....

left side .....

right side .....

### X-level with closed gate

0 mm\* .....

\*Standard



## Safety System Products

# Check list high speed roll doors

### Color door panel\*\*

blue (RAL 5007)\*

yellow (RAL 1023)

grey (RAL 7038)\*

red (RAL 3000)

orange (RAL 2004)

### Vision panel

#### transparent vision panel standard dimension

height: 600mm width: 1200mm attached ..... mm above floor level

#### transparent vision panel custom dimensions

height: ..... mm width: ..... mm attached ..... mm above floor level

#### transparent vision panel ESD standard dimension

height: 200mm width: 1200mm attached ..... mm above floor level

#### bronze vision panel Custom dimensions

height:..... mm width: ..... mm attached ..... mm above floor level

#### red vision panel for welding protection Custom dimensions

height:..... mm width: ..... mm attached ..... mm above floor level

### Black main switch on the control box\*

### Motor

position

left

right

A2-drive system for supply 1x230V\*

A2-drive system for supply 3x400V

Motor box cover required (standard with 344protec)

### External communication device

no\*

Profisafe

Profinet

.....

\*) Standard

\*\*) 2mm thick, PVC-coated, double-reinforced woven fabric including woven carbon fibers for electrostatic discharge (prEN 1718).

Sound reduction: 25dB at 2000Hz



## Safety System Products

# Check list high speed roll doors

### Display location

standard location is in the front\*

inside the control box

### Push buttons (up-stop-down)

Inside the control box\*

On the outside of the control box (front side)

### Safety

electrical safety edge with wireless connection

safety light curtain in the door frames\*

safety light curtain across the opening, instead of electrical safety edge

volts free contact, door open

volts free contact, door closed

contact less safety switches mounted in one leg\* (SAFIX)\*\*

contact less safety switches mounted in both legs montiert (SAFIX)\*\*

window in the frame over the safety switches

.....

LED indication strip on the frame,

please state side, colours and function

.....

Harting connector on motor for quick motor replacement

UPS - Uninterruptible Power Supply

### Standing frame

aluminium\*

steel

not required

### Customer specific requirements

.....

\*) Standard

\*\*) The contact switches are always connected to terminals in the control cabinet

